

GUBI 32FA STOOL FRONT UPHOLSTERED // CENTER BASE, NON STACKABLE

Photo coming soon

GUBI CHAIR COLLECTION

Designed by Komplot Design

PRODUCT COLOURS

Photo coming soon

Photo coming soon

// Blackstained beech

// Oak

Photo coming soon

// American Walnut

Item no.: 21001-32FA-XX + style code

DESCRIPTION

The GUBI Chair Collection is a chair series in laminated moulded 3-D veneer or in the injection moulded HiRek material. The shell is 5 mm thick. Both types of the shells can be delivered upholstered, with front upholstered or fully upholstered in fabric or leather. The base is available in steel, in different finishes as specified below and moulded wood in various finishes. Several of the chair versions are stackable. The GUBI Chair series includes a side chair with and without arms, a bar stool, a lounge chair and a table series in 3 different heights.

VERSION - VENEER - FRONT UPHOLSTERED

- Blackstained beech / Chrome base // Gloss level 20-30 / -
- Oak / Chrome base // Gloss level 20-30 / -
- American Walnut / Chrome base // Gloss level 20-30 / -
- Blackstained beech / Black painted base // Gloss level 20-30 / RAL 9005, gloss level 10-15
- Oak / Black painted base // Gloss level 20-30 / RAL 9005, gloss level 10-15
- American Walnut / Black painted base // Gloss level 20-30 / RAL 9005, gloss level 10-15

CHAIR VERSION

20-05-2016

Order item - look for part number in the pricelist.

The series consists of the following:

GUBI 3FA, GUBI 32FA, GUBI 33FA

FACTS

MEASUREMENT - L X W X H MM

Sitting height: 660 mm Seat width: 413 mm Seat depth: 422 mm Seat height: 157 mm

Back height: 170 mm

Frame width: 390 mm

Frame depth: 390 mm

Chair height: 780 mm Shell thickness: 5 mm

Frame thickness: Ø11 mm

Front upholstered: 10 mm

Footrest height: 200 mm

WEIGHT ITEM

xx KG

PACKAGING TYPE

Cardboard box

PACKAGING MEASUREMENT - L X W X H CM L:44 X W:44 X H:80 CM

WEIGHT PACKAGING - MATERIAL TYPE

- Delivery note: 5 g Cardboard box, FEFCO quality EB85BB: 1485 g
- Cardboard extra bottom: 272 g
- Polybag PE: 158 g
- LD-EPE foam protector: 44 g
- Strapping: 7 g

WEIGHT PACKAGING - TOTAL

6,851 kg



ACCESSORIES

FELT GLIDERS FOR HARD FLOOR AVAILABLE ON REQUEST.

LINKING DEVICE, CHAIR SUSPENSION FOR TABLES.

NUMBER OF PARCELS 1 pcs.

UPHOLSTERING - W X L - Fabric (1pcs) : 140 cm x 0,68 m

- Fabric (1pcs) : 140 cm x 0,68 m - Fabric (2pcs) : 140 cm x 0,43 m

- Leather: 0,62 m²

CLEANING AND MAINTENANCE

For cleaning **the upholstered surface**, first try to brush off the dirt gently. If this is not enough then year up the surface

If further cleaning of the padding is needed, a stain remover is recommended. The cleaning has to be gentle and must always be tested on the most invisible area of the surface before the actual cleaning. Avoid blotches by gentle, circular rubbing towards the stain.

To avoid stains, quickly remove the dirt with a piece of absorbing household wipe and clean with water and colourless washing-up liquid.

Do not use the following products for the padding:

- Undiluted cleaning liquids.
- · Bleach.
- Ammoniac
- · Soap for hard surfaces.

For dusting and light cleaning of the wooden surface and frame use a soft, dry cloth.

For further cleaning, use a soft cloth that is firmly wrung in clean water for gently wiping the surface, and then immediately use a dry cloth to wipe the surface again.

If more thorough cleaning is necessary, use a mild detergent or washing-up liquid dissolved in water on a firmly wrung cloth. Afterwards, repeat the process with clean water as described above.

Polish with a soft cloth after wiping.

Do not use materials for maintenance that:

- · Contain abrasive agents.
- Are basic, acidiferous or organic.

For the best maintenance of the product, protect it against sunlight and heat, and try to keep it away from moisture, grease and other dirt.

Furthermore, protect the surfaces against sharp objects and other that might scratch.

ENVIRONMENT

Parts can be separated and sorted for recycling.

TESTS

Foam is fire retardant according to California Technical Bulletin 117.

Foam according to BS 5852, Crib 5, is available on request

CERTIFICATION AND LABELS